

00000000 0000

- .00000000 0000 0000 00 000000 0000000 00000 .1
- 0000 000 00000000 0000 0000000 0000000 000000 000000 0000 00000 00000000 000000 00000000 00 .2
- .00000 00000 000000000
- 2.5 :0000000 00000 0000000 3 .3x90mm (7.5 0(000000x 34mm 10x 34mm.
- 4. .0000 0000000 0000000 000 000000000 0000000000 00 000 5 00 00000000 00000 0000000
- .0000000 00000000 0000000000 00000 .0000000 00000000 00000 000000000 00000000 00000000 .5
- .0000000000 0000000 0000000000 0000000 0000000000 0000 .6
- .0000000 0000 00 00000 0000000 00000 .7
- .00000000000 00000000 0000000 0000 00000000 000000 00000 00 00000 00 000000000 0000
- .(000000000 0000) 0 00000000 * 3 00 0000000000 00000000 000000 00000 00 0000000

000000000000 0000000000 00000000 0000000000 000000000 0000 0000000000 0000000000000 00000000 :00000000 00000
 .0000 0000000000

000000

- 000000 + 00000 :000000
- 34 0000000 0 00000000 90 :000000 0000mm / 3.54in & 1.34 0000in
- (000000000 0000) 000000000 0 * 3 00 0000000000 00000000 :00000000
- 240-110 00000000 :00000000 0000v 50 / 60hz 4.8 00 :00000000v 250ma
- 0000 0000000000 0000000000 :0000000000 0000000000
- 2.48 / 00000000 6.3 0000 :0000000 00000 0000in 1.8 00000000 0 00000000 2.7 0000cm / 1.06in & 0.71 0000in
- 6.8 * 10 :00000000 0000cm / 3.94 * 2.68in (l * w)


:00000000 00000000

- 000000000 00000000 00000 & 00000 000000 * 1
- 90 * 1mm 00000 0000
- 00000 0000 00000000 34 * 2
- 00000000 00000 00 * 1
- 0000000000 00000 * 1

PRODUCT SIZE



PRODUCT DETAILS



PRODUCT FEATURES


Scalable small lenses that work at different times can be selected to make work easier for three different stalls to expand the visual range




Adjust the angle



First gear




Second gear



Third gear



Large lenses



Small lenses

PRODUCT PHOTOGRAPH



