

STEREOMICROSCOPE

MULTI-FUNCTION



Product Usage



N.W	26.64kg
Objective lens	Continuous zoom 7x~45x
Eyepiece	Binocular wide angle WF10X
Power	220v-50hz, 110v-50/60hz
Transformer	Built-in 0-12v, continuous dimming
Light source on the lamp	12v/15w halogen lamp
Under light source	12v/15w halogen lamp
Eyepiece holder	45° inclination, 360° horizontal rotation 55-75mm pitch



Monitor and camera need to be purchased separately

▼ CHARACTERISTICS

The microscope is suitable for a wide range of scenarios. Use a fully coated eyepiece to increase light transmission. A pure copper objective ensures image stability. Adjustable binoculars for different distances.

Eyepiece	Standard configuration		Additional large objective					
			0.5X		1.5X		2X	
	Working distance100mm	Working distance100mm	Working distance165mm	Working distance165mm	Working distance45mm	Working distance45mm	Working distance30mm	Working distance30mm
	Magnification	Field of view	Magnification	Field of view	Magnification	Field of view	Magnification	Field of view
10X/20	7X	28.6	3.5X	57.1	10.5X	19	14X	14.3
	45X	4.4	22.5X	8.9	67.5X	3	90X	2.2



Fully coated eyepiece
for increased light transmission


Electronic circuit repair



Textile



Watch repair



Industrial assembly



Medicine



Jewelry processing
identification

LED halogen lamp



Continuous zoom hand wheel


Pure copper objective to ensure image stability



Trinocular version with TV tube
expandable electronic eyepiece CCD




ORIGINAL PHOTO



Adjustable binocular tube

SHIPPING LIST



1.EYEPIECE PARTS

2. FOCUSING BRACKET

3.10/20X EYEPIECE X2

4. EYEPIECE COVER

5.THE RACK

6.INSTRUCTIONS

7.BLACK AND WHITE DOUBLE-SIDED MAT

8.ED HALOGEN LAMP

9.THICK LARGE CARTON

10.THICKENED LARGE FOAM BOX