

# STEREOMICROSCOPE

MULTI-FUNCTION



# Product Usage



N.W	26.64kg
Objective lens	Continuous zoom 7x~45x
Eyepiece	Binocular wide angle WF10X
Power	220v-50hz, 110v-50/60hz
Transformer	Built-in 0-12v, continuous dimming
Light source on the lamp	12v/15w halogen lamp
Under light source	12v/15w halogen lamp
Eyepiece holder	45° inclination, 360° horizontal rotation 55-75mm pitch



**Monitor and camera need to be purchased separately**

## ▼ CHARACTERISTICS

The microscope is suitable for a wide range of scenarios. Use a fully coated eyepiece to increase light transmission. A pure copper objective ensures image stability. Adjustable binoculars for different distances.

Eyepiece	Standard configuration		Additional large objective					
			0.5X		1.5X		2X	
	Working distance100mm	Working distance100mm	Working distance165mm	Working distance165mm	Working distance45mm	Working distance45mm	Working distance30mm	Working distance30mm
	Magnification	Field of view	Magnification	Field of view	Magnification	Field of view	Magnification	Field of view
10X/20	7X	28.6	3.5X	57.1	10.5X	19	14X	14.3
	45X	4.4	22.5X	8.9	67.5X	3	90X	2.2



Fully coated eyepiece  
for increased light transmission


Electronic circuit repair



Textile ▲



Watch repair ▲



Industrial assembly ▲



Medicine ▲



Jewelry processing  
identification



LED halogen lamp



Continuous zoom hand wheel


Pure copper objective to ensure image stability



Trinocular version with TV tube  
expandable electronic eyepiece CCD



# ORIGINAL PHOTO



Adjustable binocular tube





1.EYEPIECE PARTS

3.10/20X EYEPIECE X2

5.THE RACK

7.BLACK AND WHITE DOUBLE-SIDED MAT

8.ED HALOGEN LAMP

9.THICK LARGE CARTON

2. FOCUSING BRACKET

4. EYEPIECE COVER

6.INSTRUCTIONS

10.THICKENED LARGE FOAM BOX