

Features

- 1) La capacità di pastella raggiungere 900mAH.
- 2) Luce a LED risparmiare energia e illuminare molto tempo
- 3) Protezione della copertura per tenere la lampada di ingrandimento privo di polvere
- 4) accende / check soldi funtion selezionare impostare "I" per illuminare, impostare "II" per il controllo di denaro.

Applicazione: Elettronica, industrie chimiche, editoria e stampa, raccolta di francobolli, la preparazione di campioni biologici, lega quinary o di produzione di gioielli, lettura, ecc

Specification

Misura della lente: 90 mm, 25 millimetri

Diottrica: 3 D, 8 D

Tensione in ingresso: AC 220 V-240 V 50-60hz

Potenza: 3.5W

Sorgente di luce: tubi fluorescenti

Intensità di illuminazione: 1100 Lux

产品描述



| | | | |
|-----------------------|----------------------------|-----------------------|-------------------------|
| Catelogy: | Desk lamp magnifying glass | Model: | BST-308 |
| Lens: | Glasses | Lens size: | 5.5mm |
| Diopter: | 5D | Voltage: | 110V/220V 50-60HZ |
| Power: | 0.5W | Light source | LED (11 LED lamp beads) |
| illuminance: | 208Lux | Life: | 5000hours |
| Body material: | Metal tube | Base material: | ABS |
| Body lenght | 37.5cm | N.W: | 380g/unit |
| Package size | 14*11.5*14cm | G.W.: | 455g/unit |

Detail show



Size



Picture

Front



Side



Lighting



Side



Package



FEATURES:

- The battery capacity is 2000mAh.
- Long service life, up to 10000 hours (with up to 500 times use).
- Charging quickly, high light and low energy consumption.
- Simple to use, easy to carry and use.
- LED light source, energy saving and long life.

USE METHOD:

- Turn on the power switch.
- When charging, the red light will flash.
- When fully charged, the red light will stop flashing.

NOTICE:

- Please do not touch the lens when the lamp is on.
- Please do not touch the lens when the lamp is off.
- Please do not touch the lens when the lamp is on.
- Please do not touch the lens when the lamp is off.

220V 110V

