BEST-939 [] [] / IC [] [





100 % 000 00 000 000

□ : - 0.09lbs (40g) / medium size - 0.04lbs (18g) / small-0.01lbs (3g)

 \square : \square . 6 in (15.3cm)


PRODUCT DISPLAY








- Install a proper IC suction header on 939 sunction pen.
- ② After installing the header, put the header on IC.



③ Press the button on the sunction pen to discharge the air, then release the button to produce vacuum suction force to pick up IC.



4 Put the IC on appointed place, press the button, the vacuum pen discharges air to let the IC fall off.



- The suction pen have three size header: samll, medium and larger.
 - 1. Larger size for 40G.
 - 2. Medium size for 18G.
 - 3. Small size for 3G.







WEIGHT:24G

FRONT



270MM

55MM

BACK