

## Features

- 1) A capacidade de atingir massa 900mAH.
- 2) Diodo emissor de luz economizar energia e iluminar muito tempo
- 3) Capa de proteção para manter a lente de aumento livre de poeira
- 4) iluminar / check dinheiro funtion seletor "I" para iluminar, defina "II" para o dinheiro de seleção.

Aplicação: Electronics, indústrias químicas, edição e impressão, coleta de selo, para preparar amostra biológica, liga quinary ou de fabricação de jóias, leitura, etc.

## Specification

Tamanho da lente: 90 mm, 25 milímetros

Dioptria: 3 D, 8 D

Tensão de entrada: AC 220 V-240 V 50-60 Hz

Potência: 3.5W

Fonte de luz: lâmpadas fluorescentes

A intensidade da iluminação: 1.100 lux

## 产品描述



<b>Catelogy:</b>	Desk lamp magnifying glass	<b>Model:</b>	BST-308
<b>Lens:</b>	Glasses	<b>Lens size:</b>	5.5mm
<b>Diopter:</b>	5D	<b>Voltage:</b>	110V/220V 50-60HZ
<b>Power:</b>	0.5W	<b>Light source</b>	LED (11 LED lamp beads)
<b>illuminance:</b>	208Lux	<b>Life:</b>	5000hours
<b>Body material:</b>	Metal tube	<b>Base material:</b>	ABS
<b>Body lenght</b>	37.5cm	<b>N.W:</b>	380g/unit
<b>Package size</b>	14*11.5*14cm	<b>G.W.:</b>	455g/unit

Detail show



# Size



Picture

Front



Side



Lighting



Side



Package



**FEATURES:**

- The battery capacity is 2000mAh.
- Long service life, 2000 hours of continuous use (up to 500 times on/off).
- Charging mode: high light and low energy (LED).
- Simple to use: simply plug and use.
- LED light source and automatic on/off.

**USE METHOD:**

- Plug the power cord into the power outlet.
- Press the power button to turn on the lamp.
- Press the power button to turn off the lamp.

**NOTICE:**

- Please do not touch the lens when the lamp is on.
- Please do not touch the lens when the lamp is off.
- Please do not touch the lens when the lamp is on.
- Please do not touch the lens when the lamp is off.
- Please do not touch the lens when the lamp is on.
- Please do not touch the lens when the lamp is off.

220V 110V

